

7028000

wolcraft®


**TYP
053**
4000x

**6
mm
1/4"**


4 006885 702806

für • for • pour • per

Arrow:

JT 21, T 27

Black & Decker:

A5751, A5752, A5980

Bosch:

HT 8, HT 14, HMT 53, PTK 14 E, PTK 3,6 LI

Einhell:

TC-CT 3,6 LI, TC-EN 20 E

Esco:

Compacta 530, Decora 530, Derby 530, Esco 10, -20, -30, -40 -50, -90, HT 53051, HT 53052, HT 53053, HT 53055

Kwb:

PT 8, PT 10, -PT 14, HT053, MT 10, T8, T9, T14, T17, TT14

Lux:

HT Mini! 196250, 195015, 195000, 195040, 195060, 195010, 195020, 195030, Decotacker

Novus:

J-01A, J-01AS, J-01, J-02, J-08 ABH, J-09 ABH, J-16 EADHG, J-17, J-18, J-19 EADHG, J-19 EAD, J-17 DA, J-102 DA, J-105 EADHG, J-214, EA J-316 A, J-08XX, J-09XX

Piranha:

X 70004, X 70005, X 70006, X 70101, X 70102

Rapid:

R53, -153, -253, -353, -453, -553, MS4.1, M10R

Rocafix:

MS 05, MS 20, MS 30, MS 40, MS 100, MS110, MS 500, ES230, HS21, MS10

Rocagrat:

Fix 102, Fix 103, Fix 106, ROC 11

Stanley/Bostitch:

Hobby 8, HD 14, Pro 8, ST 10, ST 14, Vario 14, TR45, TR150L, Hammeracker

wolcraft:

6999, tacocraft HT8, tacocraft 8, Universal-Tacker, Profi-Multifix, 7005, tacocraft 10, tacocraft 7, tacocraft 14, tacocraft P10, tacocraft P14+, tacocraft M10, tacocraft M14+, tacocraft ET14+, 7090


 Raccolta differenziata.
Verifica le disposizioni
del tuo Comune

 wolcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
www.wolcraft.com


7028000 W42



4 006885 702806