

FICHE TECHNIQUE
STC901P




Longueur (mm) : 330 (310)
Largeur (mm) : 230 (210)
Hauteur (mm) : 80 (70)
Poids (kg) : 1.20
Charge maximum (kg) : 8
Fabriqué en : aluminium / MDF / acier / PVC
Coloris : argent

Gamme : STORAGE
Code usine : C5
Code douane : 4202191000
EAN : 3321369931024

Autres :

- Malette de protection aluminium
- Extérieur en PVC
- 3 Charnières acier à l'arrière
- Coins renforcés
- Serrures à combinaisons
- Mousse prédécoupée dans le fond densité 24 kg / m3
- Mousse crantée sur le dessus
- 4 pieds pour la poser à terre



TECHNICAL SHEET

STC901P



Lenght (mm) : 330 (310)
Widht (mm) : 230 (210)
Height (mm) : 80 (70)
Weight (kg) : 1.20
Maximum load capacity (kg) : 8
Made of : aluminium / MDF / steel / PVC
Colors : silver

Range: STORAGE
Factory: C5
Custom: 4202191000
EAN : 3321369931024

Others :

- Aluminium case
- Outside wall made of PVC
- 3 steel hinges
- Reinforces corner
- Combination locks
- Precutted foam of the bottom density 24 kg / m3
- Alveolate foam on the top
- 4 feet for laying on the floor

