

Dual-Lautsprecherkabel

2 x 4,0 mm² Kabel mit einer Kombination aus reinen Kupfer- und versilberten Litzen

Dieses Lautsprecherkabel kombiniert Litzen aus reinem Kupfer mit versilberten Strängen, für eine getrennte Übertragung des Hoch-/Mitteltonbereichs und der Bassfrequenzen. Mit einem Querschnitt von 2 x 4,0 mm² sorgt der sehr feindrahtige, eng verseilte Aufbau für ein dynamisches Klangbild bei HiFi-Anlagen.

- 4 Stränge reine Kupfer- mit 3 Strängen versilberten Litzen für eine getrennte Frequenzübertragung
- feindrahtiger, eng verseilter Aufbau
- robuster und hochflexibler Außenmantel
- Plus-/Minuspol-Kennzeichnung

Technische Daten

Kabel


Typ:	2 x Rundkabel
Länge (m):	100,0
Material Innenleiter:	SPC (versilbertes, sauerstofffreies Kupfer) + OFC (sauerstofffreies Kupfer)
Durchmesser Innenleiter (mm):	2 x 630 Adern x 0,09 (2 x 4,0)
AWG:	11
Material Außenmantel:	hochelastisches PVC
Durchmesser Außenmantel (mm):	5,5 x 11,0

Signalübertragung


Übertragungsarten:	digitale und analoge Audiosignale
Kapazität (pF):	66,9
Wellenwiderstand (Ω):	4,5
Isolationswiderstand (MΩ/km):	0,6

Allgemein

Gewicht (kg):	16,7
Betriebstemperatur von / bis (°C):	-20 / +60
Garantie (Jahre):	10



Kabelquerschnitt



Artikelnr.	Kabellängen (m)	Verpackung (Maße in mm)	Gewicht (kg)	Abbildung	EAN Code
52815	100.0	Kunststoffspule: X x X x X Export VPE (1 Stk.): 340 x 340 x 205	Kunststoffspule: 16,7 Export VPE: 16,7		4 040849 528156

TARIC-Code: 85444290900

Bei Clicktronic® werden alle Kabel oberhalb einer Länge von 7,5 Metern gemäß der Testkriterien als Standard HDMI™-Kabel bezeichnet, auch wenn sie ursprünglich als High Speed HDMI™-Kabel ausgelegt wurden und ggf. auch über größere Distanzen eine deutliche Mehrleistung zeigen.

Alle enthaltenen Firmennamen und Produktbezeichnungen sind Warenzeichen der jeweiligen Inhaber. Alle Rechte vorbehalten. Bei HDMI™ handelt es sich um eine eingetragene Marke der HDMI Licensing L.L.C.

Der Inhalt kann von den Abbildungen abweichen. Druckfehler und Änderungen an Produkt, Verpackung oder Dokumentation behalten wir uns vor. Clicktronic®, Pillmannstraße 12, D-38112 Braunschweig

	10 Years Warranty	OFC	SPC
Designed in Germany	High-Quality Assurance	99,99% Oxygen Free Copper	99,99% Silver Plated Copper

Dual speaker cable

2 x 4.0 mm² cable with a combination of pure copper braids and silver-plated braids

This speaker cable combines braids made of pure copper with silver-plated strands for separate transmission of high/mid and bass frequencies. Having 2 x 4.0 mm² cross-section, the very fine-wired, tightly stranded design provides a dynamic sound for HiFi systems.

- 4 strands of pure copper with 3 silver-plated conductors for a separate transmission frequency
- fine-wired, tightly stranded design
- rugged and highly flexible outer sheath
- marking of positive/negative pole

Specifications

Cable


Type:	2 x Round cable
Length (m):	100.0
Inner conductor material:	SPC (silver plated, oxygen free copper) + OFC (Oxygen free copper)
Inner conductor diameter (mm):	2 x 630 wires x 0.09 (2 x 4.0)
AWG:	11
Outer sheath material:	highly elastic PVC
Outer sheath diameter (mm):	5.5 x 11.0

Transmission modes:


Transmission modes:	digital and analog audio signals
Capacitance (pF):	66.9
Characteristic impedance (Ω):	4.5
Insulation resistance (MΩ/km):	0.6

General

Weight (kg):	16.7
Operating temperature from / to (°C):	-20 / +60
Warranty (years):	10



Cross section



Article no.	Cable lengths (m)	Packaging dimensions (mm)	Weight (kg)	Figure	EAN Code
52815	100.0	Plastic spool: X x X x X Master carton (1 pcs.): 340 x 340 x 205	Plastic spool: 16.7 Master carton: 16.7		 4 040849 528156

TARIC Code: 85444290900

At Clicktronic® cables are designated as standard HDMI™ cables above a length of 7.5 meters, according to the test criteria, even if they originally are designed as High Speed HDMI™ cables and mostly show a significant power increase over long distances.

All company and product names are trademarks of their respective owners. All rights reserved. HDMI™ is a registered trademark of HDMI Licensing L.L.C.

The content may differ from those shown. We reserve the right for printing errors and changes to product packaging or documentation. Clicktronic®, Pillmannstraße 12, D-38112 Braunschweig/Germany

Designed in Germany	10 Years Warranty High-Quality Assurance	OFC 99,99% Oxygen Free Copper	SPC 99,99% Silver Plated Copper
---------------------	---	----------------------------------	------------------------------------