

Dual-Lautsprecherkabel

2 x 2,5 mm² Kabel mit einer Kombination aus reinen Kupfer- und versilberten Litzen

Dieses Lautsprecherkabel kombiniert Litzen aus reinem Kupfer mit versilberten Strängen, für eine getrennte Übertragung des Hoch-/Mitteltonbereichs und der Bassfrequenzen. Mit einem Querschnitt von 2 x 2,5 mm² sorgt der sehr feindrahtige, eng verseilte Aufbau für ein dynamisches Klangbild bei HiFi-Anlagen.

- 4 Stränge reine Kupfer- mit 3 Strängen versilberten Litzen für eine getrennte Frequenzübertragung
- feindrahtiger, eng verseilter Aufbau
- robuster und hochflexibler Außenmantel
- Plus-/Minuspol-Kennzeichnung

Technische Daten

Kabel

Typ:	2 x Rundkabel
Länge (m):	10,0 20,0 100,0
Material Innenleiter:	SPC (versilbertes, sauerstofffreies Kupfer) + OFC (sauerstofffreies Kupfer)
Durchmesser Innenleiter (mm):	2 x 392 Adern x 0,09 (2 x 2,5)
AWG:	13
Material Außenmantel:	hochelastisches PVC
Durchmesser Außenmantel (mm):	5,0 x 10,0


Signalübertragung

Übertragungsarten:	digitale und analoge Audiosignale
Kapazität (pF):	63,6
Wellenwiderstand (Ω):	7,4
Isolationswiderstand (MΩ/km):	0,75


Allgemein

Gewicht (kg):	1,33 2,37 11,3
Betriebstemperatur von / bis (°C):	-20 / +60
Garantie (Jahre):	10

ADVANCED



Kabelquerschnitt



Artikelnr.	Kabellängen (m)	Verpackung (Maße in mm)	Gewicht (kg)	Abbildung	EAN Code
52812	10.0	Rolle: 130 x 130 x 110 Export VPE (1 Stk.): 284 x 284 x 260	Kunststoffspule: 1.33 Export VPE: 10.64		4 040849 528125
52813	20.0	Rolle: 160 x 160 x 114 Export VPE (1 Stk.): 514 x 354 x 150	Kunststoffspule: 2.37 Export VPE: 14.22		4 040849 528132
52810	100.0	Kunststoffspule: 346 x 344 x 208 Export VPE (1 Stk.): 346 x 344 x 208	Kunststoffspule: 11,3 Export VPE: 11,3		4 040849 528101

TARIC-Code: 85444290900

Bei Clicktronic® werden alle Kabel oberhalb einer Länge von 7,5 Metern gemäß der Testkriterien als Standard HDMI™-Kabel bezeichnet, auch wenn sie ursprünglich als High Speed HDMI™-Kabel ausgelegt wurden und ggf. auch über größere Distanzen eine deutliche Mehrleistung zeigen.

Alle enthaltenen Firmennamen und Produktbezeichnungen sind Warenzeichen der jeweiligen Inhaber. Alle Rechte vorbehalten. Bei HDMI™ handelt es sich um eine eingetragene Marke der HDMI Licensing L.L.C.

Der Inhalt kann von den Abbildungen abweichen. Druckfehler und Änderungen an Produkt, Verpackung oder Dokumentation behalten wir uns vor. Clicktronic®, Pillmannstraße 12, D-38112 Braunschweig

	10 Years Warranty High-Quality Assurance	OFC 99,99% Oxygen Free Copper	SPC 99,99% Silver Plated Copper
--	---	---	---

Dual speaker cable







2 x 2.5 mm² cable with a combination of pure copper braids and silver-plated braids

This speaker cable combines braids made of pure copper with silver-plated strands for separate transmission of high/mid and bass frequencies. Having 2 x 2.5 mm² cross-section, the very fine-wired, tightly stranded design provides a dynamic sound for HiFi systems.

- 4 strands of pure copper with 3 silver-plated conductors for a separate transmission frequency
- fine-wired, tightly stranded design
- rugged and highly flexible outer sheath
- marking of positive/negative pole

Specifications

Cable	
Type:	2 x Round cable
Length (m):	10.0 20.0 100.0
Inner conductor material:	SPC (silver plated, oxygen free copper) + OFC (Oxygen free copper)
Inner conductor diameter (mm):	2 x 392 wires x 0.09 (2 x 2.5)
AWG:	13
Outer sheath material:	highly elastic PVC
Outer sheath diameter (mm):	5.0 x 10.0
Transmission modes:	
Transmission modes:	digital and analog audio signals
Capacitance (pF):	63.6
Characteristic impedance (Ω):	7.4
Insulation resistance (MΩ/km):	0.75
General	
Weight (kg):	1.33 2.37 11.3
Operating temperature from / to (°C):	-20 / +60
Warranty (years):	10

Article no.	Cable lengths (m)	Packaging dimensions (mm)	Weight (kg)	Figure	EAN Code
52812	10.0	Plastic spool: 130 x 130 x 110	Plastic spool: 1.33		
		Master carton (8 pcs.): 284 x 284 x 260	Master carton: 10.64		
52813	20.0	Plastic spool: 160 x 160 x 114	Plastic spool: 2.37		
		Master carton (6 pcs.): 514 x 354 x 150	Master carton: 14.22		
52810	100.0	Plastic spool: 346 x 344 x 208	Plastic spool: 11.3		
		Master carton (1 pcs.): 346 x 344 x 208	Master carton: 11.3		

TARIC Code: 85444290900


At Clicktronic® cables are designated as standard HDMI™ cables above a length of 7.5 meters, according to the test criteria, even if they originally are designed as High Speed HDMI™ cables and mostly show a significant power increase over long distances.

All company and product names are trademarks of their respective owners. All rights reserved. HDMI™ is a registered trademark of HDMI Licensing L.L.C.

The content may differ from those shown. We reserve the right for printing errors and changes to product packaging or documentation. Clicktronic®, Pillmannstraße 12, D-38112 Braunschweig/Germany

	10 Years Warranty	OFC 99,99% Oxygen Free Copper	SPC 99,99% Silver Plated Copper
Designed in Germany	High-Quality Assurance		

ADVANCED



Cross section