


15pcs Grease filled Electrical Wire Splice Connector Set

Item No. 1905C129



Feature:

- Self-Stripping
- Moisture resistant
- Waterproof
- 3 Wire U-contact



Specification

Insulation material: Polyamide
Contact material: Tinned Brass
Color: Blue cap / White base
Wire range: AWG 20 -15 (0.5-1.65mm²)
Wire outer diameter: 3,8 mm (max.)
Conductor diameter: 0,8 ~ 1,4 mm
Voltage rating: 300V max.
Current rating: 5A max
Working temperature: 0-85°C
Working humidity: 95% RH
Package qty.: 15pcs

Dimension

