

## VIEW4



3 days of use



Super Wide Angle  
& Blur effect



Ultra-large storage



## 3 days use in 1 charge

Experience 3 days of boundless energy. View4 provides an extra long-life battery in a single charge. The smartphone features a Super Wide Angle triple camera, ultra-large memory and prismatic design.

**Available colours:** ● Cosmic Blue ● Cosmic Gold ● Cosmic Green

### CUSTOMISED ACCESSORIES

- **Smart Folio** with standing option to enjoy your content hands-free
- **Slim Clear Case** with hard back cover and flexible frame
- Ultra-resistant **Printed Tempered Glass** that protects your phone against scratches

Hauptmerkmale	
Mobilfunknetzwerke	4G LTE B1 (2100)/ B3 (1800)/ B5 (850) / B7 (2600)/ B8 (900) / B20 (800) / B28B(700) / B40 (2300) H+/3G+/3G HSPA+ 850/ 900/ 1900/ 2100 MHz GSM/GPRS/EDGE 850/900/1800/1900 MHz
Datenrate	FDD-LTE Cat.4 DL 150 Mbps, UL 50 Mbps
Betriebssystem	Android™ 10
Prozessor	Mediatek 6762D A25, Octa-Core 1.8 GHz
Grafikkarte - GPU	IMG PowerVR GE8320
Dual SIM	2 Nano SIM
Design	Touch screen
Erhältlich in den Farben	Cosmic Blue, Cosmic Gold, Cosmic Green with a special effect prism light reflexion. Finish : Glass-like
Abmessungen	165.7 x 75.8 x 8.85 mm
Gewicht	180
Akku	5000 mAh Li-Po
Standby-Zeit	Up to 882h
Gesprächszeit	Up to 63.4h
Interner Speicher (ROM)	64GB
Arbeitsspeicher (RAM)	3GB
Speicher erweiterbar	Micro SD card up to 256GB
Beschleunigungssensor	Ja
Kompass (Magnetometer)	Ja
Annäherungssensor	Ja
SAR-Wert	Head: 0.377W/Kg, Body: 1.686 W/Kg, Limb:3.136W/Kg
Bildschirm	
Abmessungen	6.52
Typ	IPS Technology, 450 nits brightness
Farbe	16.7M
Auflösung	HD+ (1600 x 720 pixels), pixel density: 269 PPI
Multi touch	Ja
Konnektivität	
WLAN / Wi-Fi	802.11 b/g/n
Tethering & Mobiler Hotspot	USB, Bluetooth, Access Point Wi-Fi
Bluetooth Version	4.2
USB OTG	Ja
USB Anschluss	2.0
PC Synchronisation	Ja
Kopfhörerausgang	3.5mm jack
Foto & Video	
Kamera	Triple: 13MP (Main) + 2MP (Depth) + 5MP (114° Super Wide Angle)
Optionen	Face Beauty, Night mode, HDR, Time Lapse, Slow Motion, AI mode, Super Wide Angle, Bokeh mode, Google Lens, Live filter

Blitzlicht	Ja
Frontkamera	8MP
Digital Zoom	4x
Autofokus	No
Bildeditor	Ja
Weissabgleich	Auto, Incandescent, Daylight, Fluorescent, Cloudy
Videoaufnahmen	1080p@30fps

#### Multimedia und Unterhaltung

Stereo FM Radio	Ja
Audio Formate	MP3, MIDI, AAC, AMR
Bild Formate	JPEG, GIF, PNG, BMP
Video Formate	3GPP, MP4, 3GP, H.264

#### GPS

GPS	Ja
A-GPS	Ja

#### Personalisierung

Sprachen	English, French, Italian, German, Dutch, Spanish, Portuguese, Russian, Czech, Polish, Finnish, Hungarian, Arabic, Urdu, Persian, Danish, Norwegian, Swedish, Thai, Indonesian, Vietnamese, Turkish, Cyrillic Serbian, Latin Serbian, Slovenian, Macedonian, Croatian, Catalan, Basque, Romanian, Polish, Slovak, Ukrainian, Greek
Wiko features	Face Unlock, Wiko Launcher, One Handed Mode, Simple Mode, Smart Assist, Smart Action, Google Assistant Button

#### Google™ Mobile Service

Google Apps	Ja
-------------	----

#### Packungsinhalt

	Headset
Kurzanleitung	Google Assistant user guide
	Micro USB Kabel Netzteil Wiko Mobiltelefon

Änderung der technischen Daten vorbehalten. Der Zugriff auf Google™-Anwendungen kann je nach Land abweichen.



Der SAR-Wert (spezifische Absorptionsrate) der Mobiltelefone, fasst den maximalen Expositionspegel an elektromagnetischen Wellen, für eine Nutzung am Ohr, in Zahlen zusammen. Die europäische Regelung verlangt, dass die SAR 2W/kg nicht übersteigt.  
© Wiko. Alle Rechte vorbehalten. Wi-Fi ist eine Marke der Wi-Fi Alliance. Bluetooth ist eine Marke von Bluetooth SIG. Alle anderen Warenzeichen sind das Eigentum ihrer jeweiligen Betreiber