



CD12F/0B-050C4

Stecker



Micro Detectors

Italian Sensors Technology



Elektrische Daten

Nennstrom	4 A
Led	No
Polzahl	4
Nennspannung	Max . 250Vac/dc

Mechanische Daten

Jacket color	RAL 7035 - Grigio
Gasket material	FKM
Nut material	Acciaio inox AISI316L
Conductors diameter including isolation	Ø 1,27mm ± 0,02mm
Number of bending cycles	4000000
Traversing path	≤ 10 m
Anzugsdrehmoment	0,4 Nm
Traversing rate	≤ 3 m/s
Betriebstemperatur	-40°C ÷ +105°C (posa fissa) -25°C ÷ +105°C (movimentazione)
Torsion force	± 270°/m (4000000 cicli di torsione, max. 25 cicli di torsione/min)
Länge (m)	5
Kopftyp	90°

Außendurchmesser	Ø 4,7mm ± 0,15mm
Material Außenmantel	PP-EPDM
Isolierungsmaterial	PP
Mindestbiegeradius	> 10 x D (movimentazione) > 5 x D (posa fissa)
Leiter Querschnitt	4 x 0,34 mm ² (42 x 0,10 mm ²)
Acceleration	≤ 10 m/s ⁴

Test/Zertifizierungen

Schutzart	IP65 / IP67 / IP68 / IP69K
-----------	----------------------------

M.D.Micro Detectors S.p.A.

Strada S.Caterina, 235
41122 Modena (MO)
Tel. 059 420411
Fax 059 253973
E-mail info@microdetectors.com

Druckdatum

29/06/2020 16:23:13