


HANNSpad 133 Titan 3 – 13.3" FHD Wi-Fi

THINK BIGGER


The new Android based, large screen HANNSpad Titan 3 Tablet PC is the perfect hosts for eBooks, multimedia entertainment, online socializing and much more.



13.3" / 33,78 cm

Part. No.: SN14TP1B2AS04



SIZE, RESOLUTION




CPU, RAM MEMORY



CAMERA, STORAGE



Wi-Fi, BATTERY




Technical Specifications >>>

Name / Part Nr.	HANNSpad Titan 3 / SN14TP1BAS
Screen Size	33.78 cm / 13.3 Inch
Resolution (H x V)	1920 x 1080 Full HD, 16:9 Aspect Ratio
Viewing Angle	178° (V) / 178° (H)
Touchscreen Type	10 Point Capacitive Multi Touch Panel
CPU	Octa Core CPU RK3368 Cortex ARM A53 64 bit, up to 1.5 GHz
GPU	PowerVR SGX6110 up to 600 MHz, OpenGL 3.1
Memory	2GB DDR3 RAM
Storage Internal	16GB NAND FLASH
Storage External	Micro-SD/Micro-SDHC Card, max. 32GB
WLAN	Wi-Fi IEEE 802.11 b/g/n
Bluetooth	Bluetooth 4.1
Camera	Front 2MP / Rear 5MP with AutoFocus
Microphone	Built-in
Speakers	Built-in, Stereo Speakers 2 x 1W, 8 ohm
Headphone Output	3.5mm Stereo Earphone
HDMI	Mini HDMI, support 1080P
GPS	No
G-Sensor	Yes
3 Axis Accelerometer	Yes
USB	Micro USB 2.0 + Micro USB Host (OTG)
Battery Type	Li-Ion Battery 10.000 mAh, 3.7 Volt
Battery Life	>5 hours (1080p Video playback, Wi-Fi On, Brightness 80%, Speaker max.) *
Power Adaptor	DC 5V, 2.5A

Operating Temperature	0 ~ 45° Celsius
Operating Humidity	10 ~ 85%
Case Material	Metal + Plastic (PC + ABS) for back cover
Product Dimensions	337 x 220 x 11.5 (W x H x D mm)
Packaging Dimensions	383 x 249 x 54 (W x H x D mm)
Net Weight	1060 grams
Gross Weight	-
Control Keys	Power, Volume +/-
Operating System	Android 9
UI Language	Android default
Accessory	1 Power Adaptor with EU and UK clips, 1 USB Cable (100 cm), 1 OTG Cable (8 cm), Quick Start Guide, Warranty Card
Certification	CE EMC, R&TTE, LVD, RoHS, REACH, WEEE
Packaging	Color retail box
EAN Code	4711404023101

PART. NO.:
SN14TP1B2AS04



4 711404 023101 >