



D-SC1800H Specifications




|                                |             |
|--------------------------------|-------------|
| Nominal Capacity               | 1800mAh     |
| Nominal Voltage                | 1.2V        |
| Internal Impedance (at 1000Hz) | < 8mΩ       |
| Charge                         |             |
| Standard Charge (1C)           | 180mA x 15h |
| Trickle Charge (0.05C)         | 90mA x 1.2h |
| Discharge Cut-off Voltage      | 1.0V        |
| Max Dimension (with tube)      |             |
| Diameter                       | 23.0mm      |
| Height                         | 43.0mm      |
| Weight                         | 49 g        |
| Ambient Temperature            |             |
| Standard charge                | 0 ~ 60℃     |
| Trickle charge                 | 0 ~ 60℃     |
| Discharge                      | -20 ~ 70℃   |
| Storage                        | -20 ~ 45℃   |


Standard charge characteristics



Trickle charge characteristics



Discharge characteristics



Charge efficiency

