




1
 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

—	3,0	9,2	UNPLATED	ARCAP	3-828101-3
—	3,0	9,2	TINPLATED	BRASS	3-828101-1
—	11,0	17,2	UNPLATED	ARCAP	2-828101-3
—	11,0	17,2	TINPLATED	BRASS	2-828101-1 1
—	9,7	15,9	UNPLATED	ARCAP	1-828101-3
—	9,7	15,9	TINPLATED	BRASS	1-828101-1
—	5,0	11,2	UNPLATED	ARCAP	828101-3
—	5,0	11,2	TINPLATED	BRASS	828101-1
—	DIM "B"	DIM "A"	FINISH	MATERIAL	ORDERNUMBER

—	—	—	—	—	CUSTOMER DRAWING					FOR REFERENCE ONLY WILL NOT BE UPDATED	
—	—	—	—	—	© COPYRIGHT 19 —					BY AMP HOLLAND B.V.	
—	—	—	—	—	ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE					COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.	
—	—	—	—	—	THIS DRAWING IS UNPUBLISHED					RELEASED FOR PUBLICATION —,19 —	
—	—	—	—	—						AMP HOLLAND B.V. 's—Hertogenbosch, The Netherlands.	
F1	REVISED PER ECO-09-023313		KK	AEG	120CT09	NAME					
F	H-9720		S.M.	C.V.T	21-04-92	SCREWLOCK,FEMALE,HD—SERIES					
LTR.	REVISION RECORD		DR.	CHK.	DATE						
DR.: D.KESSLER		CHK.: C.V.TILBURG		APP.: L.V.SOEST		DWG.No.			REV.LTR.	SHEET	
DATE: 02-04-91		DATE: 23-04-91		DATE: 25-04-91		828101			F1	1 OF 1	A4