


ClassicPhono
by **Lenco**

Turntable with Bluetooth® Reception, Built-in Speakers and Rechargeable Battery

TT-120



Stream from smartphone

EN

- Bluetooth 5.0
- Retro suitcase turntable
- 3 rated speed settings: 33 RPM, 45 RPM and 78 RPM
- Belt drive
- Auto stop
- 2 built-in speakers
- Integrated rechargeable battery up to 5 hours
- Ceramic stereo cartridge with stylus
- MDF cabinet with P.U. leather finishing
- Connections: RCA output, Headphone out, Aux in

DE

- Bluetooth 5.0
- Koffer-Plattenspieler im Retro-Stil
- 3 Geschwindigkeiten: 33 U/min, 45 U/min und 78 U/min
- Riemenantrieb
- Auto-Stopp
- 2 eingebaute Lautsprecher
- Integrierter Akku bis zu 5 Stunden
- Keramik-Tonabnehmer mit Nadel
- Holzgehäuse mit Kunstlederoberfläche
- Anschlüsse: RCA-Ausgang, Kopfhörer-Ausgang, AUX-Eingang

NL

- Bluetooth 5.0
- Retro platenspeler
- 3 snelheden: 33 OPM, 45 OPM en 78 OPM
- Riemaandrijving
- Auto stop
- 2 ingebouwde luidsprekers
- Oplaadbare batterij tot 5 uur
- Keramische stereo cartridge met naald
- MDF kabinet met namaaklederen finishing
- Aansluitingen: RCA uitgang, Hoofdtelefoon uitgang, AUX ingang

FR

- Bluetooth 5.0
- Tourne-disque rétro
- 3 réglages de vitesse, 33, 45 et 78 tours
- Courroie d'entraînement
- Arrêt automatique
- 2 haut-parleurs intégrés
- Batterie rechargeable intégrée jusqu'à 5 heures
- Cellule céramique stéréo
- Caisson en bois recouvert de simili cuir
- Connexions: Sortie RCA, Sortie Casque, Entrée Auxiliaire

ES

- Bluetooth 5.0
- Maleta retro para tocadiscos
- 3 velocidades: 33 RPM, 45 RPM y 78 RPM
- Transmisión por correa
- Parada automática
- 2 altavoces incorporados
- Batería recargable integrada hasta 5 horas
- Cartucho de cerámica estéreo con lápiz
- Carcasa MDF con acabado en imitación de piel
- Conexiones: Salida RCA, Auriculares salida, Entrada AUX

DATA :

- Power source: AC 230V, 50Hz
- Power consumption max: 8W
- Dim. unit: 350 x 110 x 255 mm (WxDxH)
- Gift box Dim. Unit: 382 x 150 x 345 mm (WxDxH)
- Net/Gross Weight: 2,6 kg / 3,1 kg
- Master Carton quantity: 1 pc
- Custom code: 8519300000
- EAN-code: 8711902044918

Container quantity :
20' ft : 1200 pcs
40' ft : 2430 pcs
40'HQ : 2780 pcs

Subject to changes without prior notice



V8 12-1-2021