





“Schutzvermerk nach DIN ISO 16016 beachten” “Please pay attention to copyright note DIN ISO 16016”




A-A (1 : 1)




ISO (1 : 1)





B-B (1 : 1)




Oberteil
Lid




C-C (1 : 1)



Z (2 : 1)



Y (2 : 1)



Für Version mit Einlegedichtung:

Schutzart IP40. Um Schutzart IP65 zu erreichen, muss die beiliegende Dichtung korrekt montiert werden. Die Dichtung darf in den Ecken weder gestreckt noch gestaucht werden. Stoßstelle schräg geschnitten und verklebt, sodaß die Schnittstellen durch den Federdruck aufeinander gedrückt werden.

For Version with enclosed gasket

Protection class IP40. To achieve protection class IP65, the enclosed gasket must be mounted correctly. The gasket must not be stretched or compressed in the corners. Ends cut obliquely and glued, so that the cut ends are pressed together by the spring pressure.

BOX^{4U}		Datum/Date		Name/name		Zeichnungs-Nr. /	
						Drawing-No.: 2K 5455.106.01	
		Gezeichnet	29.01.2025	MG		6U-090908	
		Kontrolliert				Katalogzg./Catalogue draw.	
		Norm				2504976.idw	
Status	Ä.Nr./Alt.No	Datum/Date	Name			A2	