



HK126

Product Specifications

Model no.	HK126
Styling	In-ear
Color version	Black
Connectivity	Wireless
Bluetooth version	5.2
RF Freq.	2.402 - 2.480 GHz
Bluetooth profile	HSF, AVRCP, A2DP
Codec	SBC
Maximum RF Power (dBm)	6
Antenna type	FPC
Operation distance	>10 m
Multi-point	Yes- 2 devices
Speaker Driver	
Driver size (mm)	10 mm
Frequency response	20-20 KHz
Sensitivity dB @ 1KHz +/- 3dB	110
Impedance	32 ohm
Max power	5 mW
Voice Assistant	
Push to trigger voice assistant on mobile phones (on headset remote)	Yes

Tele-communication	
Microphones	1 x mic
Sensitivity dB @ 1KHz +/- 3dB	-38
Playtime (hours) 75% iPhone volume	
Play Music	7.5 hrs
Talk time	6.5 hrs
Standby time	60 hrs
Charging	
Extra Playtime with charging case	
HP Charging time	< 3.5 hrs full charge; 70 min for 2 hrs
HP Charging port	USB-C
Battery type & capacity (Earbud)	Lithium polymer, 80 mAh
Battery weight	approx. 2.5g
Headset/Earbuds output power	5mW
Battery charge lifecycle (Full charge lifecycle)	≥300 cycles
UI (control)	
Buttons	1 x button control
LED	Blue & Red (on earbud)
Jacks / plugs	
Charging	USB-C
Accessories	
Cables (length)	USB cable (300 mm Length)
Ear Caps	Silicon Ear caps (S/M/L)
Others	Detectable earhook
Packaging	
Retail box	Paper box with window
No. pack / outer	5
Total Weight (including packaging)	330 g
Outer carton box Dimensions (LxWxH)	207x112x120 mm

Earbuds Product Dimensions (LxWxH)	59.29x48.16x20.34 mm
Earbuds weight	9.8 g
Packaging Dimensions (LxWxH)	110x110x39 mm
Packaging Weight (gross) (including USB charging cable, QSG, silicon caps & warranty sheet)	64 g
Operating temperature	0℃ ~+45℃
Storage temperature	-20℃ ~+70℃