

2510 : Bending Spring - For Copper Pipe



Description

Outside bending spring.

Hardened, burnished steel wire. End bending rings.
Wall thickness: 0,8 to 1,2 mm.

References

Sku	Ø mm	L mm	kg
251010	10	240	0,170
251012	12	240	0,240
251014	14	255	0,280
251015	15	275	0,320
251016	16	285	0,350
251018	18	295	0,470
251020	20	325	0,580
251022	22	340	0,650

