



GREENMNKY®

Specifications of Glassmaster

Model		GREENMNKY - GLASSMASTER
Function		Automatic Screen Protector Applying Machine
Category		Tempered Glass Screen Protector
Supporting Models		iPhone X - iPhone 17 ProMax Samsung Galaxy S22 - S26
Supporting Payments		NAYAX、CCV
Printing Invoice		Upon request
Capacity	Number of Slots	96
	Capacity of Single Slot	0~40
	Total Capacity	3840
Appearance	Product Dimension	1000mm × 920mm × 1800mm (Including Casters)
	Packaging Dimension	1130mm x 1030mm x 2000mm (Eco-friendly Honeycomb Carton)
	Net Weight	400 kgs
	Gross Weight	500 kgs (Machine Only)
	Screen Type & Size	32 inch capacitive touch screen
Electric Parameter	Nominal Voltage	220V / 110V
	Standby Current	1.2A
	Standby Power	280W
	Rated Power	600W

