

**Accessories**  
**ETA 1170 21 6A**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

Similar to illustration

**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

|            |                                   |
|------------|-----------------------------------|
| Type       | ETA 1170 21 6A                    |
| Order No.  | <a href="#">1278760000</a>        |
| Version    | Accessories, Circuit breaker, 6 A |
| GTIN (EAN) | 4050118091342                     |
| Qty.       | 5 pc(s).                          |

## Data sheet

### Accessories ETA 1170 21 6A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 9.8 mm  | Width (inches)  | 0.386 inch |
| Height     | 22 mm   | Height (inches) | 0.866 inch |
| Depth      | 51.6 mm | Depth (inches)  | 2.031 inch |
| Net weight | 9.6 g   |                 |            |

### Temperatures

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |
|----------------------------------|--------|----------------------------------|--------|

### Material data

|        |       |
|--------|-------|
| Colour | black |
|--------|-------|

### System specifications

|         |                |
|---------|----------------|
| Version | Fuse cartridge |
|---------|----------------|

### Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Plugged |
|---------------------|-----------------|------------------|---------|

### Rating data

|               |         |               |     |
|---------------|---------|---------------|-----|
| Rated voltage | 28 V DC | Rated current | 6 A |
|---------------|---------|---------------|-----|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 6.0   | EC000035    | eClass 6.2 | 27-14-20-90 |
| eClass 7.1 | 27-14-20-90 | eClass 8.1 | 27-14-20-90 |
| eClass 9.0 | 27-14-20-01 | eClass 9.1 | 27-14-20-01 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |                              |
|------------------|------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD</a> |
|------------------|------------------------------|