

Data Sheet

Recommended Application: Universal

Long Life Extra
4103
 Conrad:650745

| | |
|-------------------------------|---------------------------------------|
| Type Designation | 4103 |
| Designation IEC | LR03 |
| System | Zn-MnO ₂ (Alkaline) |
| Shelf Life (Coding)* | 5 years |
| Nominal Voltage [V] | 1.5 |
| Typical Capacity C [mAh] | 1200 (discharge with high-resistance) |
| Permissible Temperature Range | - 10 °C ... 50 °C |
| Weight, approx. [g] | 11 |
| Volume [ccm] | 3.8 |

Dimensions [mm]

min: max:

| | | |
|---|------|------|
| Ø | 9.5 | 10.5 |
| A | - | 44.5 |
| B | 43.3 | - |
| C | 4.3 | - |
| E | - | 0.5 |
| F | - | 3.8 |
| G | 0.8 | - |

