

SPECIFICATION FOR 04B-8XC2

Model No. : 04B-8XC2

Issue Date: 2012-05-04

1. The specification of the cable: Φ 0.19mm*21 /2

2. Max current allowable : 2.5A

3. Environmental Requirements

- | | |
|----------------------------|---------------------------|
| 3.1 Operating Temperature: | 0°C To 40°C |
| 3.2 Storage Temperature: | -20°C To 60°C |
| 3.3 Operating Humidity: | 20%-85% Rh Non-Condensing |
| 3.4 Storage Humidity: | 10%-90% Rh Non-Condensing |

4. Cable Length: 1.8m

5. Output plugs:

(1) 8XC2

A=2.5MM, B=3.5MM, H=3.5*1.35MM, D=5.0*2.1MM, G=5.5*2.5MM, N=5.5*1.5MM,
I= 4.0*1.7MM, S=2.35*0.75MM

6. Device Colour:


Black

7: WEIGHT

83 g MAX exclude packing

8. Mechanical Specification:

Consult Attached Drawing



APPROVE:

AUDITING:

CONNER: