

3-WAY SPEAKER GTx 663 ES

165 mm/ 6,6" | 240 Watt Max. Power



Subject to availability and technical modification.

Highlights

Start of sales

Spring 2019

Order number

2 003 017 123 459

EAN- Code

4 260 499 850 074

- 3-way triaxial speaker
- 165 mm/ 6,6" diameter
- 240 watts maximum power handling
- 50 watts nominal power handling
- Injected PP- membrane (glossy black)
- Extended pole design (EXP)
- Gold plated connectors
- High-quality design grille
- Installation depth only 55,5 mm/ 2,19"
- Accessories: including design grille, cables, mounting material, installation instructions



3-WAY SPEAKER GTx 663 ES

165 mm/ 6,6" | 240 Watt Max. Power

2/4

Technical data:

- System 3-way triaxial
- Diameter 165 mm/ 6,6"
- Maximal power handling 240 watts
- Nominal power handling 50 watts
- Nominal impedance 4 ohms
- Frequency response 40- 22.000 Hz
- Efficiency (2,83V/1 m) 93 dB
- Cone material Injected PP membrane
- Basket material Steel, crinkle black
- Connectors 2,8/ 4,8 mm, gold plated
- Installation depth 55,5 mm/ 2,19"
- Diameter installation hole 144 mm/ 5,67"
- Accessories Design grille, cables, mounting material, installation instructions



3-WAY SPEAKER **GTx 663 ES**

165 mm/ 6,6" | 240 Watt Max. Power

3/4

Overview of GTx ES Series 2019



100mm/4"

GTx 402 ES

Peak power handling	140 watts
RMS power handling	30 watts
Impedance	4 ohms
Frequency response	90- 20.000 Hz
Sensitivity	90 dB (2.83 V/ m)



130mm/ 5,4"

GTx 542 ES

Peak power handling	180 watts
RMS power handling	40 watts
Impedance	4 ohms
Frequency response	70- 20.000 Hz
Sensitivity	91 dB (2.83 V/ m)



165mm/ 6.6"

GTx 662 ES

Peak power handling	220 watts
RMS power handling	45 watts
Impedance	4 ohms
Frequency response	55- 22.000 Hz
Sensitivity	92 dB (2.83 V/ m)



165mm/ 6.6"

GTx 663 ES


Peak power handling	240 watts
RMS power handling	50 watts
Impedance	4 ohms
Frequency response	40- 22.000 Hz
Sensitivity	93 dB (2.83 V/ m)

3-WAY SPEAKER GTx 663 ES

165 mm/ 6,6" | 240 Watt Max. Power

4/4


Logistics data



GTx 402 ES

9 cartons per each layer, 6 layers totally
6PRS per each carton (12PCS)
324PRS totally (648PCS)


QTY: 6 PRS
N.W.: 5.5 KGS
G.W.: 10 KGS
CTN: 321X301X225mm



GTx 542 ES

9 cartons per each layer, 6 layers totally
6PRS per each carton (12PCS)
324PRS totally (648PCS)


QTY: 6 PRS
N.W.: 6.6 KGS
G.W.: 11 KGS
CTN: 362X345X252mm



GTx 662 ES

4 cartons per each layer, 5 layers totally
6PRS per each carton (12PCS)
120PRS totally (240PCS)

QTY: 6 PRS
N.W.: 8.5 KGS
G.W.: 16 KGS
CTN: 460X412X270mm



GTx 663 ES

4 cartons per each layer, 5 layers totally
6PRS per each carton (12PCS)
120PRS totally (240PCS)

QTY: 6 PRS
N.W.: 8.5 KGS
G.W.: 13.5 KGS
CTN: 410X394X270mm