

SENTRON, cylindrical fuse link, 14x51 mm, 40 A, gG, Un AC: 500 V



Versie	
productmerknaam	SENTRON
productbenaming	cilindrisch smeltpatroon
Algemene technische gegevens	
bedrijfsklasse van de smeltpatroon	gG
grootte van de smeltpatroon	14 x 51 mm
type spanning	AC
stroom / bij AC / nominale waarde	40 A
voedingsspanning / bij DC	250 V
bedrijfsspanning / nominale waarde	500 V
Losbandigheid	
vermogensverlies [W] / bij nominale waarde stroom / bij AC / bij warme bedrijfstoestand / per pool	4,5 W
Hoofd-circuit	
bedrijfsstroom / nominale waarde	40 A
Product Details	
productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal

nettogewicht

22 g

Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NW6117-1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW6117-1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW6117-1

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

