

SENTRON, cylindrical fuse link, 14x51 mm, 12 A, aM, Un AC: 690 V



Versie	
productmerknaam	SENTRON
productbenaming	cilindrisch smeltpatroon
Algemene technische gegevens	
bedrijfsklasse van de smeltpatroon	aM
grootte van de smeltpatroon	14 x 51 mm
type spanning	AC
stroom / bij AC / nominale waarde	12 A
voedingsspanning / bij DC	250 V
bedrijfsspanning / nominale waarde	690 V
Losbandigheid	
vermogensverlies [W] / bij nominale waarde stroom / bij AC / bij warme bedrijfstoestand / per pool	0,69 W
Hoofd-circuit	
bedrijfsstroom / nominale waarde	12 A
Product Details	
productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal

nettogewicht

21 g

## Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

## Verdere informatie

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NW8106-1>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW8106-1>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW8106-1](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW8106-1)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

