

SETRON, cylindrical fuse link, 10 x 38 mm, 20 A, gPV, Un DC:  
1000 V



Versie	
productmerknaam	SETRON
productbenaming	cilindrisch smeltpatroon

  

Algemene technische gegevens	
bedrijfsklasse van de smeltpatroon	gPV
grootte van de smeltpatroon	10x38 mm
type spanning	DC
stroom / bij AC / nominale waarde	20 A
voedingsspanning / bij DC	1 000 V
bedrijfsspanning / nominale waarde	1 000 V

  

Hoofd-circuit	
bedrijfsstroom / nominale waarde	20 A

  

Product Details	
productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	10 g

  

Certificaten	
--------------	--

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

Verdere informatie

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NW6007-4>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW6007-4>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW6007-4](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6007-4)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>