

SENTRON, cylindrical fuse link, 14x51 mm, 4 A, gG, Un AC: 690 V



Versie

productmerksnaam	SENTRON
productbenaming	cilindrisch smeltpatroon

Algemene technische gegevens

bedrijfsklasse van de smeltpatroon	gG
grootte van de smeltpatroon	14 x 51 mm
type spanning	AC
stroom / bij AC / nominale waarde	4 A
bedrijfsspanning / nominale waarde	690 V

Hoofd-circuit

bedrijfsstroom / nominale waarde	4 A
----------------------------------	-----

Product Details

productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	21 g

Certificaten

referentiemarkering	
---------------------	--

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

General Product Approval

[Miscellaneous](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NC1504>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NC1504>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1504

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>