

Class J fuse link 40 A 600 V quick-response, respect national installation rules!



Wersja	
Nazwa markowa produktu	SETRON
oznaczenie produktu	Wkładka bezpiecznika cylindrycznego
wykonanie produktu	konstrukcja cylindryczna

  

Ogólne dane techniczne	
charakterystyka wkładki bezpiecznikowej	szybki
wielkość wkładki bezpiecznikowej	Class J
rodzaj napięcia	AC
prąd / przy AC / wartość znamionowa	40 A
napięcie robocze / wartość znamionowa	600 V

  

Obwód główny	
prąd roboczy / wartość nominalna	40 A

  

Szczegóły produktu	
element składowy produktu / sygnalizator uderzenia	Nigdy
pozycja montażowa	dowolnie, najlepiej pionowo
masa netto	76 g

  

Certyfikaty	
-------------	--

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

### General Product Approval



### Więcej informacji

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW4217-1HG>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW4217-1HG>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW4217-1HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4217-1HG)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



