

SENTRON, cylindrical fuse holder, 10x38 mm, 3-pole, In: 30 A, Un AC: 600 V, Flat version



Wersja	
Nazwa markowa produktu	SENTRON
oznaczenie produktu	Uchwyt bezpiecznika cylindrycznego
wykonanie produktu	wersja płaska
Ogólne dane techniczne	
liczba biegunów	3
wielkość wkładki bezpiecznikowej	10 x 38 mm
Napięcie zasilania	
prąd / przy AC / wartość znamionowa	30 A
napięcie robocze	600 V
• przy AC / wartość znamionowa	
Stopień ochrony IP	IP20
Konstrukcja mechaniczna	
wysokość	76 mm
szerokość	60,5 mm
głębokość	26 mm
masa netto	103 g

Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F
F

General Product Approval



[Miscellaneous](#)

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC1038-3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/3NC1038-3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1038-3

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



