

SENTRON, cylindrical fuse link, 14x51 mm, 4 A, gG, Un AC: 690 V



Wersja

Nazwa markowa produktu	SENTRON
oznaczenie produktu	Wkładka bezpiecznika cylindrycznego

Ogólne dane techniczne

charakterystyka wkładki bezpiecznikowej	gG
wielkość wkładki bezpiecznikowej	14x51 mm
rodzaj napięcia	AC
prąd / przy AC / wartość znamionowa	4 A
napięcie robocze / wartość znamionowa	690 V

Obwód główny

prąd roboczy / wartość nominalna	4 A
----------------------------------	-----

Szczegóły produktu

element składowy produktu / sygnalizator uderzenia	Nigdy
pozycja montażowa	dowolnie, najlepiej pionowo
masa netto	21 g

Certyfikaty

oznaczenie środków roboczych	
------------------------------	--

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

General Product Approval

[Miscellaneous](#)

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC1504>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/3NC1504>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1504

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>