

## Safety Instructions



0,1,2,4,5b,7,8,9,11,12,  
15,16,17,20,21,22,  
23A+25,26B+19C



Info Hotline

+49 (0) 5041 998 389

Mon. - Do. 7<sup>00</sup> - 20<sup>00</sup>










Fr. 7<sup>00</sup> - 17<sup>00</sup>

Paulmann Licht GmbH  
31832 Springe / Germany  
www.paulmann.com



Art.-Nr.:  
507000020

(+MA 173)

PBO 10/09



60 %				Wärmeverteilung Répartition de la chaleur Warmteverdeling Heat distribution Distribución térmica
40 %				
20 %				SECURITY AKZENT
80 %				



	[mm]	Akzent Security [W]	Coolbeam [W]	Stiftsockel [W]	[mm]	[m]	[mmØ]	[mm]	[cm]	[°]	[°]	[mm]	[mm]
<b>A</b>		110	50	50		51	0.5	92	60	≥20	20		8-20
		85	35	35		35	0.5	64	50	≥20	20		5-20
		83	50	35		51	0.5	73	60	≥20			5-20
		64	35	20		35	0.5	57	50	≥20			5-20
<b>B</b>		69x79	35	35		45x51	0.5	60	$\frac{60}{\nabla\nabla >110}$	≥20			5-20
		68x68	35	35		37x37	0.5	64	$\frac{60}{\nabla\nabla >110}$	≥20			5-20
		92	50	35		51	0.5	76	60	≥20	20		5-20
		99	50	35		51	0.5	86	$\frac{60}{\nabla\nabla >110}$	≥20	45		3-20
		79	50	35		51	0.5	70	$\frac{60}{\nabla\nabla >110}$	≥20			5-20
		55	35	20		35	0.5	51	$\frac{50}{\nabla\nabla >110}$	≥20			5-20
		83	50	50		51	0.5	68	$\frac{60}{\nabla\nabla >110}$	≥20	30		5-20
		66	35	20		35	0.5	60	$\frac{50}{\nabla\nabla >110}$	≥20	30		5-20
	91	35	35		51	0.5	73	60	≥20	20		5-20	
<b>C</b>		50			20	G4 Gy6.35		40	>30	≥10			5-20
		70			20	G4	0.2	60		≥10		>25	5-20
		72			20	G4	0.2	64		≥10		>25	5-20
		66			20	G4	0.2			≥10			5-20
		66			20	G4	0.2	54		≥10		>25	5-20
		69			20	G4	0.2	60		≥10	17	>25	5-20

X = Farbgebung, Couleurs, Colour, Colores