

SENTRON, cylindrical fuse link, 14x51 mm, 40 A, gG, Un AC: 500 V



Versão	
Nome da marca do produto	SENTRON
Designação do produto	Encaixe de fusível cilíndrico
Dados técnicos gerais	
Classe de operação do elemento fusível	gG
Tamanho do elemento fusível	14x51 mm
Tipo de tensão	CA
Corrente / com AC / valor estipulado	40 A
Tensão de alimentação / com DC	250 V
Tensão de serviço / valor estipulado	500 V
Dissipação	
Potência de perda [W] / com valor de corrente estipulado / com AC / com estado de funcionamento quente / por pólo	4,5 W
Circuito principal	
Corrente de funcionamento / valor nominal	40 A
Detalhes do produto	
Componente do produto / Detector de choque	Não

Posição de montagem	opcional, preferível vertical
Peso líquido	22 g

Certificados

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW6117-1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW6117-1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6117-1

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

