

SENTRON, cylindrical fuse link, 10 x 38 mm, 20 A, gPV, Un DC:
1000 V



Versão	
Nome da marca do produto	SENTRON
Designação do produto	Encaixe de fusível cilíndrico
Dados técnicos gerais	
Classe de operação do elemento fusível	gPV
Tamanho do elemento fusível	10x38 mm
Tipo de tensão	CC
Corrente / com AC / valor estipulado	20 A
Tensão de alimentação / com DC	1 000 V
Tensão de serviço / valor estipulado	1 000 V
Circuito principal	
Corrente de funcionamento / valor nominal	20 A
Detalhes do produto	
Componente do produto / Detector de choque	Não
Posição de montagem	opcional, preferível vertical
Peso líquido	10 g
Certificados	

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW6007-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW6007-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6007-4

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>