

Class J fuse link 30 A 600 V time-lag, respect national installation rules!



| Versão | |
|--------------------------|-------------------------------|
| Nome da marca do produto | SETRON |
| Designação do produto | Encaixe de fusível cilíndrico |
| Execução do produto | estrutura cilíndrica |

| Dados técnicos gerais | |
|--|-------------------|
| Classe de operação do elemento fusível | de ação retardada |
| Tamanho do elemento fusível | Classe J |
| Tipo de tensão | CA |
| Corrente / com AC / valor estipulado | 30 A |
| Tensão de alimentação / com DC | 300 V |
| Tensão de serviço / valor estipulado | 600 V |

| Circuito principal | |
|---|------|
| Corrente de funcionamento / valor nominal | 30 A |

| Detalhes do produto | |
|--|-------------------------------|
| Componente do produto / Detector de choque | Não |
| Posição de montagem | opcional, preferível vertical |
| Peso líquido | 46 g |

Certificados

Indicadores de referência

- segundo a DIN EN 61346-2 F
- segundo a IEC 81346-2:2009 F

General Product Approval



Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW4112-2HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW4112-2HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4112-2HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



