

Class J fuse link 70 A 600 V quick-response, respect national installation rules!



Versão	
Nome da marca do produto	SETRON
Designação do produto	Encaixe de fusível cilíndrico
Execução do produto	com contacto de lâmina
Dados técnicos gerais	
Classe de operação do elemento fusível	rápido
Tamanho do elemento fusível	Classe J
Tipo de tensão	CA
Corrente / com AC / valor estipulado	70 A
Tensão de serviço / valor estipulado	600 V
Circuito principal	
Corrente de funcionamento / valor nominal	70 A
Detalhes do produto	
Componente do produto / Detector de choque	Não
Posição de montagem	opcional, preferível vertical
Peso líquido	76 g
Certificados	

#### Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

#### General Product Approval



#### Outras informações

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW4323-1HG>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW4323-1HG>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW4323-1HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4323-1HG)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



