

SENTRON, cylindrical fuse link, Class CC, 3 A, quick, Un AC: 600 V, respect national installation rules!



| версия | |
|--|--|
| Фирменное название продукта | SENTRON |
| Наименование продукта | Цилиндрическая предохранительная вставка |
| Общие технические данные | |
| Эксплуатационный класс вставки предохранителя | Безынерционный |
| Размер вставки предохранителя | Класс срабатывания CC |
| Вид напряжения | перем. ток |
| Ток / при переменном токе / расчетное значение | 3 A |
| рабочее напряжение / расчетное значение | 600 V |
| Главная цепь | |
| Рабочий ток / номинальное значение | 3 A |
| Подробнее | |
| Компонент продукта / сигнализатор удара | нет |
| Монтажное положение | Произвольно, предпочтительно вертикально |
| вес-нетто | 6 g |
| Сертификаты | |
| Условное обозначение | |

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



CSA

UL

EG-Konf.

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NW2030-0HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW2030-0HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW2030-0HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

