

Class J fuse link 300 A 600 V quick-response, respect national installation rules!



версия	
Фирменное название продукта	SENTRON
Наименование продукта	Цилиндрическая предохранительная вставка
Исполнение продукта	С ножевыми контактами
Общие технические данные	
Эксплуатационный класс вставки предохранителя	Безынерционный
Размер вставки предохранителя	Класс срабатывания J
Вид напряжения	перем. ток
Ток / при переменном токе / расчетное значение	300 A
рабочее напряжение / расчетное значение	600 V
Главная цепь	
Рабочий ток / номинальное значение	300 A
Подробнее	
Компонент продукта / сигнализатор удара	нет
Монтажное положение	Произвольно, предпочтительно вертикально
вес-нетто	720 g
Сертификаты	

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

**General Product Approval**



Дополнительная информация

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NW4550-1HG>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW4550-1HG>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW4550-1HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4550-1HG)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



