

SENTRON, cylindrical fuse link, 14x51 mm, 4 A, gG, Un AC: 690 V



версия

Фирменное название продукта	SENTRON
Наименование продукта	Цилиндрическая предохранительная вставка

Общие технические данные

Эксплуатационный класс вставки предохранителя	gG
Размер вставки предохранителя	14x51 мм
Вид напряжения	перем. ток
Ток / при переменном токе / расчетное значение	4 А
рабочее напряжение / расчетное значение	690 V

Главная цепь

Рабочий ток / номинальное значение	4 А
------------------------------------	-----

Подробнее

Компонент продукта / сигнализатор удара	нет
Монтажное положение	Произвольно, предпочтительно вертикально
вес-нетто	21 g

Сертификаты

Условное обозначение	
----------------------	--

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

General Product Approval

[Miscellaneous](#)

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NC1504>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NC1504>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1504

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>