

**Industriellt Ethernet
IE-FCM-RJ45-C**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Servicegränssnitt FrontCom[®] Micro med RJ45 i IP65

Allmänna beställningsdata

Typ	IE-FCM-RJ45-C
Art.nr.	1018790000
Artikelbeteckning	FrontCom Micro RJ45 koppling
GTIN (EAN)	4032248730056
Frp	10 Stück

**Industriellt Ethernet
IE-FCM-RJ45-C**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data**Mått och vikter**

Väggjocklek, max.	3 mm	Väggjocklek, min.	1 mm
Nettovikt	36,4 g		

Temperaturer

Driftstemperatur, max	70 °C	Driftstemperatur, min.	-40 °C
Drifttemperatur	-40 °C...70 °C	Lagertemperatur	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Allmänna data

Tightening torque fixing nut	2 Nm	Anslutning 1	RJ45
Anslutning 2		Artikelbeskrivning	FrontCom Micro RJ45 koppling
	RJ45	Kapslingsmaterial	PA UL 94 V0
Färgkod	svart	Kontaktyta	Guld över nickel
Kategori	Cat.6 _A / Class E _A (ISO/IEC 11801 2010)	Avskärmning	360° skärmkontaktering
Monteringstyp	Kopplingskåp, Distribution box	Stickcykler	750
Skyddsklass	IP65, i slutet tillstånd		

Elektriska egenskaper

PoE / PoE+	motsvarande IEEE 802.3at
------------	--------------------------

Normer

Kontaktton Norm	IEC 60603-7-5 1	Certifikat-Nr. (cULus)	E316369
-----------------	-----------------	------------------------	---------

Klassificeringar

ETIM 3.0	EC001134	ETIM 4.0	EC001134
ETIM 5.0	EC001134	ETIM 6.0	EC001121
eClass 5.1	27-25-05-04	eClass 6.2	27-25-05-04
eClass 7.1	27-25-05-04	eClass 8.1	19-17-01-25
eClass 9.0	27-44-03-90	eClass 9.1	27-18-90-90

Godkännanden

Godkännanden



ROHS	Uppfyllelse
------	-------------

**Industriellt Ethernet
IE-FCM-RJ45-C**


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Tekniska data**Downloads**

Användardokumentation	MAN IE GUIDE DE MAN IE GUIDE EN
Broschyr/Katalog	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI FRONTCOM EN PI PROFINET CABLING EN
Godkännande/Certifikat/Dokument om överensstämmelse	DUXR.E316369
Teknikuppgifter	EPLAN, WSCAD, Zuken E3.S

**Industriellt Ethernet
IE-FCM-RJ45-C**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Ritningar**Profilritning****Montageurtag**