

**Klippon EBi QL (Essential Box industrial - Quarter Lock)
KEBI QL 303022 S2B0****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

For many years, the name Klippon® has stood for competence and quality in enclosures. The Klippon® EBi industrial enclosure series protects your components reliably if they are used in moderate environmental conditions and is designed for everyday applications. With the ever-increasing need for individual application solutions, the Klippon® EBi with its high degree of protection and impact resistance is ideally suited to your needs. Our standard product is the Klippon® EBi QL – with hinged door and double-bit key lock. A variant with mounting screws is also available, but is only manufactured on request and is subject to a minimum order quantity. DNV GL and cULus approvals are also available on request.

Allmänna beställningsdata

Typ	KEBI QL 303022 S2B0
Art.nr.	2470710000
Artikelbeteckning	Klippon EBi QL (Essential Box industrial - Quarter Lock), Tom kapsling, Rostfria stål kapslingar, Höjd: 299.5 mm, Bredd: 299.5 mm, Djup: 220 mm, Material: Rostfritt stål 1.4301 (304), borstad, Silver
GTIN (EAN)	4032248336081
Frp	1 Stück

Klippon EBi QL (Essential Box industrial - Quarter Lock)

KEBI QL 303022 S2B0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data

Mått och vikter

Bredd	299,5 mm	Byggbredd (tum)	11,791 inch
Höjd	299,5 mm	Bygghöjd (tum)	11,791 inch
Djup	220 mm	Byggdjup (tum)	8,661 inch
Montagemått bredd	250 mm	Montagemått höjd	250 mm
Väggjocklek, max.	1,25 mm	Väggjocklek, min.	1,25 mm
Nettovikt	5 384 g	Diameter	9 mm

Allmänna uppgifter

Användningsområden	Hamnanläggningar, Maskintillverkning, Transportväsende, Fartygsbyggnad, Förpackningsindustri, Processindustri	Materialtjocklek	1,25 mm
Materialtjocklek fläns	1,25 mm	Materialtjocklek kapsling	1,25 mm
Materialtjocklek lock	1,25 mm	Monteringsanvisning	Svetsad montagevinkel, Montageplatta
Normer	DIN EN 62208, IEC 60529	Tätningmaterial för lock	Skummad PUR
Öppningsvinkel lock	125 °	Material	Rostfritt stål 1.4301 (304)
Tätningmaterial	Skummad PUR	Yta	borstad
Driftstemperatur, min.	-40 °C	Driftstemperatur, max	85 °C
Slagtålighet	10.00 J	Skyddsklass	IP66
Kapslingens fastsättning	Fästörön, Installation genom kapslingens bakvägg	Fastsättning av lock	Kvartslåsning med spårinsats
Komponentfastsättning	skruvad		

Certifikatnummer kapsling

Certifikat-Nr. (cULus) E243298

Jordning kapsling

Jordning, kapsling, extern	Jordning, kapsling, intern	Påsvetsad M6 jordskruv i rostfritt stål i kapslingsunderdel och lock.
Jordning, kapsling, lock	M6 jordtapp	Påsvetsad M6 jordskruv i rostfritt stål i kapslingsunderdel och lock.

Klassificeringar

ETIM 6.0	EC000261	eClass 6.2	27-14-91-07
eClass 9.0	27-18-01-01	eClass 9.1	27-18-92-90

Godkännanden

Godkännanden



ROHS Uppfyllelse

Skapandedatum den 9 juli 2019 15:10:30 CEST

Katalogversion 07.06.2019 / Tekniska ändringar förbehållna

Datablad

Klippon EBi QL (Essential Box industrial - Quarter Lock)
KEBI QL 303022 S2B0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Tekniska data

Downloads

Teknikuppgifter Data

[STEP](#)

