

DIAZED base NDZ 25 A 500 V AC DC Top contact/top contact



Figure similar

Versiyon	
ürün marka adı	SETRON
ürün tanımı	Sigorta sistemi DIAZED
ürün modeli	DIAZED yuvası, baş kontağı / baş kontağı
sigorta yuvası modeli	Ek master
Genel teknik veriler	
kutup sayısı	1
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	NDz
Besleme gerilimi	
akım / AC'de / anma değeri	25 A
besleme gerilimi / AC'de / anma değeri	500 V
Ürün Detayı	
ürün bileşeni / kapak	Hayır
Mekanik Tasarım	
yükseklik	49 mm
genişlik	29 mm

derinlik	44,6 mm
net ağırlık	65 g
malzeme / mahfaza	Porselen

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F
F

Declaration of Conformity



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SF1012>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SF1012>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF1012

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



