

SITOR fuse link, with slotted blade contacts, NH1, In: 450 A, aR, Un AC: 690 V, Un DC: 440 V, front indicator



Versiyon

ürün marka adı	SETRON
ürün tanımı	SITOR sigorta buşonu
ürün modeli	Yarıklı bıçaklı kontaklar ile
gösterge sensörü modeli	Ön gösterge
anahtar kontak modeli	vidalama mandalları ile, gümüş
sigorta elemanı modeli	SITOR, NH tipi

Genel teknik veriler

sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	NH1
sigorta soketinin çalışma sınıfı	aR

Besleme gerilimi

gerilim türü	AC/DC
akım / AC'de / anma değeri	450 A
besleme gerilimi	
• AC'de / anma değeri	690 V
• DC'de	440 V

Ürün Detayı

ürün açıklaması	Karıştırma yok
-----------------	----------------

Aksesuar / teslimat kapsamına dahil	Vidanın sabitlenmesi için oluklu ölçer kontaklarına sahip, bağlantı boyutu: 80 mm
-------------------------------------	-----------------------------------------------------------------------------------

Mekanik Tasarım

montaj pozisyonu	isteğe bağlı, tercihen dikey
------------------	------------------------------

Çevresel koşullar

ortam sıcaklığı	-20 ... +50 °C
Çevre kategorisi	% 95 bağıl nemde -20 ila +50

Sertifikalar

referans işareti	
• DIN EN 61346-2 uyarınca	F
• IEC 81346-2:2009 uyarınca	F

General Product Approval

Declaration of Conformity



UR



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NE8233-3MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NE8233-3MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE8233-3MK

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



