

Class J fuse link 40 A 600 V quick-response, respect national installation rules!



### Versiyon

ürün marka adı	SETRON
ürün tanımı	Silindirik sigorta
ürün modeli	silindirik yapı tarzı

### Genel teknik veriler

sigorta soketinin çalışma sınıfı	hızlı
sigorta soketinin büyüklüğü	Sınıf J
gerilim türü	AC
akım / AC'de / anma değeri	40 A
işletim gerilimi / anma değeri	600 V

### Ana devre

işletim akımı / nominal değer	40 A
-------------------------------	------

### Ürün Detayı

ürün bileşeni / darbe dedektörü	Hayır
montaj pozisyonu	isteğe bağlı, tercihen dikey
net ağırlık	76 g

### Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval



Diğer bilgiler

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NW4217-1HG>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/tr/ps/3NW4217-1HG>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW4217-1HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4217-1HG)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



