

SIVACON, 开关柜- 空外壳, 无侧壁, 符合 IEC 62208 标准, IP40, 高: 2200 mm, 宽: 1000 mm, 温度: 1000 mm



版本	
产品品牌名称	SIVACON
产品名称	开关柜空壳
产品的规格	符合 IEC 62208
表层的结构形式	粉末涂层
产品的规格 / EMC结构形式	不

防护等级	
防护等级 IP	IP40
设备保护等级	防护等级 1

适应性	
安装的适宜性 / 对于米制测量	是
<b>对于一体化集成的适宜性</b>	
• 明线安装	是的
• 嵌入式安装	不
应用适宜性 / 适于外部应用	不

外形	
RAL 颜色编码	RAL 7035
颜色	淡灰色的

产品详细信息	
产品组件	
• 通风门	不
• 安装板	是的
• 后门	不
• 检视门	不
• 深度可调节的安装板	是的
产品特点 / 外壳的 / 可顺序排列的壳体	是的

数	
锁件数目	0
门的数目	2

机械设计	
高度	2 200 mm
宽度	1 000 mm
深度	1 000 mm
紧固类型	
• 19 寸内置设备	不
• 地面安装	是的
• 墙壁安装	不
净重	182 kg
材料	钢

证书	
参考标示	
• 符合 DIN EN 61346-2	U
• 符合 IEC 81346-2:2009	UC

General Product Approval	Declaration of Conformity	Test Certificates	other
		<a href="#">Special Test Certificate</a>	<a href="#">Miscellaneous</a>



[Special Test Certificate](#)

[Miscellaneous](#)

### 更多信息

**Information- and Downloadcenter (产品目录, 产品介绍册, ...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (网上订购系统)**

<https://mall.industry.siemens.com/mall/zh/zh/Catalog/product?mlfb=8MF1200-3BR4>

**Service&Support (用户手册, 操作说明书, 认证证书, 特性曲线, 常见问题,...)**

<https://support.industry.siemens.com/cs/ww/zh/ps/8MF1200-3BR4>

**图片数据库 (产品照片, 2D比例图, 3D模型, 设备电路图, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF1200-3BR4](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1200-3BR4)

**CAX-Online-Generator**

<http://www.siemens.com/cax>



