

故障电流保护开关，2 极，型号 AC，输入：16 A，10 mA，Un  
AC：230 V



版本	
产品品牌名称	SENTRON
产品名称	剩余电流保护开关
产品的规格	可选 SIGRES

一般技术数据	
极数	2
安装设备的结构尺寸 / 根据 DIN 43880	1
防电击接触保护	手指和手背安全
抗短路电流稳定性	10 kA
断路器 / 基础类型	5SV4
机械式使用寿命 ( 转换周期 ) / 典型	10 000
开关功能 / 短暂延迟	不
过压类别	III




电源电压	
电流 / AC 时 / 测定值	16 A
<ul style="list-style-type: none"> <li>供电电压 / 用于测控设备 / 最小值</li> <li>测定值</li> </ul>	100 V 50 Hz

防护等级	
------	--

防护等级 IP	IP20，安装分电器时，带连接导线
<b>交换容量</b>	
电流通断能力 / 符合 IEC 61008-1 / 测定值	0.5 kA
<b>耗散</b>	
损耗功率 [W] / 电流测定值时 / AC 时 / 在热运行状态中 / 每个电极	0.7 W
<b>电力</b>	
脱扣故障电流 / 测定值	10 mA
<ul style="list-style-type: none"> <li>• 额定电流 <math>I_n</math> / IEC，DIN / VDE / 在 40 Cel 时</li> <li>• 额定电流 <math>I_n</math> / IEC，DIN / VDE / 45 Cel 时</li> <li>• 额定电流 <math>I_n</math> / IEC，DIN / VDE / 在 50 Cel 时</li> <li>• 额定电流 <math>I_n</math> / IEC，DIN / VDE / 55 Cel 时</li> <li>• 额定电流 <math>I_n</math> / IEC，DIN / VDE / 在 60 Cel 时</li> <li>• 额定电流 <math>I_n</math> / IEC，DIN / VDE / 65 Cel 时</li> <li>• 额定电流 <math>I_n</math> / IEC，DIN / VDE / 在 70 Cel 时</li> </ul>	16 A 12.44 A 9.32 A 6.82 A 4.94 A 3.68 A 0 A
故障电流类型	AC
$I_2t$ 值 / 许可	58 000 A <sup>2</sup> ·s
工作频率	50 Hz
<b>产品详细信息</b>	
产品特点 / 无硅	是的
产品扩展 / 可安装 / 辅助装置	是的
<b>连接</b>	
可连接的导线截面	
<ul style="list-style-type: none"> <li>• 单芯线的</li> <li>• 多芯线</li> </ul>	0.75 ... 35 mm <sup>2</sup> 0.75 ... 35 mm <sup>2</sup>
拧紧扭矩 / 螺栓连接时	2.5 ... 3 N·m
位置 / 电源连接电缆	顶部或底部
<b>机械设计</b>	
高度	90 mm
宽度	36 mm
深度	70 mm
安装深度	70 mm
宽度分配单元的数量	2
紧固类型	DIN 导轨 (REG)
装入位置	任意的
<b>环境条件</b>	
环境温度	-25 ... +45 °C
<ul style="list-style-type: none"> <li>• 存放期间</li> </ul>	-40 ... +75 °C
<b>证书</b>	
参考标示	

- 符合 DIN EN 61346-2
- 符合 IEC 81346-2:2009

F  
F

General Product Approval		Declaration of Conformity	other	Railway
 CCC	 IMQ	 EG-Konf.	<a href="#">Miscellaneous</a>	<a href="#">Vibration and Shock</a>

Railway
<a href="#">Confirmation</a>

### 更多信息

**Information- and Downloadcenter (产品目录, 产品介绍册, ...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (网上订购系统)**

<https://mall.industry.siemens.com/mall/zh/zh/Catalog/product?mlfb=5SV4111-0>

**Service&Support (用户手册, 操作说明书, 认证证书, 特性曲线, 常见问题,...)**

<https://support.industry.siemens.com/cs/ww/zh/ps/5SV4111-0>

**图片数据库 (产品照片, 2D比例图, 3D模型, 设备电路图, ...)**



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SV4111-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SV4111-0)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



-CB

