# Industrial Ethernet
# IE-SFP-1GSXLC-T

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- IEEE 802.3z-compliant (Gigabit modules)
- IEEE 802.3u-compliant (Fast Ethernet modules)
- Symmetric LVPECL I/Os (Gigabit modules)
- Symmetric PECL I/Os (Fast Ethernet modules)
- TTL signal detection indicator
- In operation insertable duplex LC connector
- Class 1 laser product, EN60825-1 compliant
- -40 to 85°C operating temperature (T models)

## General ordering data

| | |
|---|---|
| Type | IE-SFP-1GSXLC-T |
| Order No. | 1286700000 |
| Version | SFP-Modul, -20 °C...+75 °C, Gigabit-Ethernet, Multimode, LC connectors, 500 m |
| GTIN (EAN) | 4050118077261 |
| Qty. | 1 pc(s). |

# Industrial Ethernet
# IE-SFP-1GSXLC-T

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Technische Daten

### Dimensions and weights

| | |
|---|---|
| Net weight | 25 g |

### EMC conformity and approvals

| | |
|---|---|
| Security | UL, TÜV |

### Environmental conditions

| | | | |
|---|---|---|---|
| Humidity | 5 to 95 % (non-condensing) | Operating temperature, max. | 75 °C |
| Operating temperature, min. | -20 °C | Storage temperature, max. | 85 °C |
| Storage temperature, min. | -40 °C | | |

### Guarantee

| | |
|---|---|
| Time interval | 3 years |

### Interfaces

| | | | |
|---|---|---|---|
| Ethernet ports | 1 | Plug-in connector | Duplex-LC |

### Order data

| | | | |
|---|---|---|---|
| Operating temperature | -20 °C...+75 °C | SFP alternatives | Gigabit-Ethernet, Multimode, LC connectors, 500 m |

### Classifications

| | | | |
|---|---|---|---|
| eClass 6.2 | 19-17-01-90 | eClass 7.1 | 19-17-01-90 |

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Downloads

| | |
|---|---|
| Declaration of Conformity | K4230912.pdf |