SAIE-7/8"S-3-0.2U-PG13.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Similar to illustration



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-7/8"S-3-0.2U-PG13.5
Order No.	1292340000
Version	Built-in plugs, 7/8", PG 13.5, No. of poles: 3, 0.2 m
GTIN (EAN)	4050118088359
Qty.	1 pc(s).

SAIE-7/8"S-3-0.2U-PG13.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	42 g

General data

Cable gland	PG 13.5	Cable length	0.2 m
Conductor O.D.	-	Contact material	CuZn
Contact surface	Gold-plated	Contact tube diameter	7/8"
Core cross-section	0.75 mm²	Housing main material	Zinc diecast, nickel-plated
Material	PUR/ PUR	No. of poles	3
Plugging cycles	≥ 100	Protection degree	IP 67
Rated current	10 A	Rated current	8 A (4- and 5-pole), 10 A (3-pole)
Rated voltage	300 V	Strand cable length	0.2 m
Temperature range of housing	-25...+85 °C	Type of connection	Pin

Classifications

eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02

Approvals

Approvals	c UL us
ROHS	Conform

SAIE-7/8"S-3-0.2U-PG13.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

