SAISM-4/8S-M12-4P D-COD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



M12 plug-in connector in IP 67 available with crew or tension clamp connection

General ordering data

Type	SAISM-4/8S-M12-4P D-COD
Order No.	1892120000
Version	Sockets prefabricated to customer spec., Plugs prefabricated to customer spec., M12, pin, straight
GTIN (EAN)	4032248569380
Qty.	1 pc(s).

SAISM-4/8S-M12-4P D-COD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	47 g

General Info

Contact surface	Gold-plated	Contact tube diameter	M12
Housing main material	CuZn	Plugging cycles	≥ 100
Protection degree	IP 67	Sheath diameter, max.	8 mm
Sheath diameter, min.	6 mm		

Electrical properties

Insulation resistance	10^8 Ω	Rated voltage	250 V

Standards

Connector standard	IEC 61076-2-101	Certificate No. (cURus)	E307231

Classifications

ETIM 3.0	EC002062	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-26-07-02
eClass 7.1	27-44-01-02		

Approvals

Approvals	ME25
ROHS	Conform