SAK Series
BS 25 IH/GN SAKT1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image



Current and voltage transformer wiring
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Type	BS 25 IH/GN SAKT1
Order No.	0335600000
Version	SAK Series, Set of fixings
GTIN (EAN)	4008190113490
Qty.	50 pc(s).

SAK Series
BS 25 IH/GN SAKT1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	5.5 mm	Width (inches)	0.217 inch
Height	5.5 mm	Height (inches)	0.217 inch
Depth	28.7 mm	Depth (inches)	1.13 inch
Net weight	1.78 g	Diameter	3 mm

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Material data

Material	Steel	Colour	green

System specifications

Version	for cross-connection link

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in

Dimensions

Diameter	3 mm

Classifications

ETIM 3.0	EC001741	ETIM 4.0	EC000897
ETIM 5.0	EC000897	ETIM 6.0	EC002848
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-92-14	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-92		

Approvals

ROHS	Conform

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP