# GWDR PO (flat gasket - polyethylene)
# GWDR PG9-PO

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

## General ordering data

| | |
|---|---|
| Type | GWDR PG9-PO |
| Order No. | 1719450000 |
| Version | GWDR PO (flat gasket - polyethylene), Sealing ring, PG 9, Polyethylene |
| GTIN (EAN) | 4008190352707 |
| Qty. | 100 pc(s). |

# GWDR PO (flat gasket - polyethylene)
# GWDR PG9-PO

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Technical data

### Dimensions and weights

| | |
|---|---|
| Net weight | 0.15 g |

### Width

| | |
|---|---|
| Thickness | 2 mm |

### General information

| | | | |
|---|---|---|---|
| Cable glands | PG | Diameter of sealing ring | 19 mm |
| External thread | PG 9 | Inside diameter D2 | 15.2 mm |
| Material | Polyethylene | O.D. | 19 mm |
| Operating temperature range, max. | 90 °C | Operating temperature range, min. | -30 °C |
| Sealing | PE-HD | Thickness | 2 mm |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 3.0 | EC000781 | ETIM 4.0 | EC000441 |
| ETIM 5.0 | EC000441 | ETIM 6.0 | EC000441 |
| UNSPSC | 31-16-18-18 | eClass 5.1 | 23-07-90-90 |
| eClass 6.2 | 27-14-91-09 | eClass 7.1 | 27-14-91-09 |
| eClass 8.1 | 27-14-91-09 | eClass 9.0 | 27-43-03-19 |
| eClass 9.1 | 27-14-44-90 | | |

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Downloads

| | |
|---|---|
| Brochure/Catalogue | CAT 3 HDC 17/18 EN<br>CAT 5 ENCL 17/18 EN |
| Engineering Data | EPLAN, WSCAD |
| Engineering Data | STEP |

# GWDR PO (flat gasket - polyethylene)
# GWDR PG9-PO

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Drawings

