




	G1	G2	H	L	sw
20905	G1/4	G3/8	9	14	19

Operating temperature:	*max. 150°C*	*dependent on temperature range of tube/ pipe used*
Operating pressure:	*up to 60bar*	*depndent on pressure range of tube/ pipe used and used temperature*
Material:	*CW614N and CW617N*	
	polished/ nickel-plated	
Thread:	*cyl. thread DIN EN ISO 228*	
	con. thread DIN EN ISO 10226	
	metr. thread DIN ISO 262	
Medium:	*pneumatic, oil-hydraulic and hydraulic circuits*	