With incised sealing ring for adjustment to several cable diameters
Fewer sizes need to be kept in stock



Robust

Application range
Brass cable gland with hexagonal fitting and variable incised sealing ring.

Design
PG connection thread

Note
Refer to SKINDICHT® EV for additional accessories
Counter nut to be used: SKINDICHT® SM

Remark
Viton® is a registered trademark of DuPont de Nemours
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	SVRE 42
Incised sealing ring ØF (mm):	35.5/39/42.5/46
SW1/SW2 mm:	57 / 54
Overall length, C (mm):	43,6
Thread length, D (mm):	10
Pieces / PU:	10
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread Available with PG 11 to 36 with VITON® incised ring
Material:	Body: nickel-plated brass Incised seal: CR
Protection rating:	IP 54
Temperature range:	-20°C to +80°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.