





Aufsteck - Stromwandler

Plug - in current transformers

ASK 31.3

Primärleiter <i>Primary conductor</i>	30 x 10 mm 2 x 20 x 10 mm
Rundleiter <i>Round conductor</i>	∅ 26,0 mm
Wandlerbreite <i>Transformer width</i>	60 mm
Schnappbefestigung <i>Snap-on-mounting</i>	Nr./no. 53011
Plombierplatte <i>Sealed shutter</i>	Nr./no. 59040



Artikelnummer	Primärstrom	Sekundärstrom	VA	Klasse
Order no.	Primary nominal current	Sec. current		Class
7011	100	5	1,5	0,5
7012	100	5	2,5	0,5
7013	150	5	1,5	0,5
7014	150	5	2,5	0,5
7015	200	5	1,5	0,5
7016	200	5	2,5	0,5
7017	200	5	5,0	0,5
7018	250	5	1,5	0,5
7019	250	5	2,5	0,5
7020	250	5	5,0	0,5
7021	300	5	1,5	0,5
7022	300	5	2,5	0,5
7023	300	5	5,0	0,5
7025	400	5	5,0	0,5
7026	400	5	5,0	0,5
7028	500	5	2,5	0,5
7029	500	5	5,0	0,5
7031	600	5	2,5	0,5
7032	600	5	5,0	0,5
7035	750	5	2,5	0,5
7036	750	5	5,0	0,5

Artikelnummer	Primärstrom	Sekundärstrom	VA	Klasse
Order no.	Primary nominal current	Sec. current		Class
7038	50	5	1,0	1
7039	60	5	1,0	1
7040	75	5	1,0	1
7041	75	5	1,5	1
7042	80	5	1,5	1
7043	80	5	2,5	1
7044	100	5	1,5	1
7045	100	5	2,5	1
7046	150	5	1,5	1
7047	150	5	2,5	1
7048	200	5	1,5	1
7049	200	5	2,5	1
7050	200	5	5,0	1
7051	250	5	1,5	1
7052	250	5	2,5	1
7053	250	5	5,0	1
7054	250	5	10,0	1
7055	300	5	1,5	1
7056	300	5	2,5	1
7057	300	5	5,0	1
7058	300	5	10,0	1
7059	400	5	1,5	1
7060	400	5	2,5	1
7061	400	5	5,0	1
7062	400	5	10,0	1
7063	500	5	2,5	1
7064	500	5	5,0	1
7065	500	5	10,0	1
7066	600	5	2,5	1
7067	600	5	5,0	1
7068	600	5	10,0	1
7069	600	5	15,0	1
7070	750	5	2,5	1
7071	750	5	5,0	1
7072	750	5	10,0	1

