Glass fibre-reinforced for maximum mechanical stability
Supporting surface for spanner means scratches on the housing are avoided



Assembly time

Temperature-resistant

Variety of approval certifications

Application range
For locking SKINTOP® cable glands in boreholes without thread.

Design
PG connection thread

Norm references / Approvals
UL File Nr. E79903

Note
UL approval only when used with the UL-approved SKINTOP® polyamide cable glands
Designed for use with SKINTOP® ST(R)

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	GMP-GL 48
SW (mm):	70
Pieces / PU:	25
On request:	Available without collar (without surface for assembling tool)
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Polyamide, glass fibre-reinforced
Temperature range:	-20°C to +100°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.







PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.